

| REV. | ECN. NO. | APPD. |
|---|---|---|
| A | | |


NOTES:
Current Rating: 2.0AMP
Withstand Voltage: 500V AC/DC
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩMin
Operation Temperature: -40℃ to +105℃

Contact Material: Phosphor Bronze
Contact plating: Au or Sn over Ni
Insulator Material: PA6T+30%G.F UL94V-0





Recommended P.C.B Layout(TOP Side)
(PCB BOARD TOLERANCE±0.05)




SECTION B-B




## *Ordering Information*

MTF263-1XXSY1

No.of Pins per ROW:02~40PIN

| | | | | |
|---|---|---|---|---|
| X. ± 0.30 | X.° ± 5° | UNITS mm | NAME(INTENDED USE) | MINTRON CO.,LTD. |
| .X ± 0.20 | .X° ± 2° | MAT'L | | |
| .XX ± 0.10 | .XX° ± 1° | | PART NO.(INTENDED USE) | TITLE: MTF263-1XXSY1 |
| .XXX ± 0.05 | .XXX° ± 0.5° | FINISH | APPD: SUNNY | DWG NO.: |
| FEMALE HEADER CONNNECTOR | | Q'TY | CHKD: LISA | |
| | | | DR: ZOE 2006-11-28 | SCALE 1 / 1 · SHEET 1 / 1 · REV. A |