


G-Switch Specification:


1.Current rated: 0.5A AC/DC
2.Voltage rating: 50V AC/DC
3.Withstanding voltage: 200V AC
4.Contact resistance: 30mΩ max.
5.Insulation resistance: 800MΩ min
6.Durability cycle: 20Cycles
7.Removal force: 0.04kgf/Pin min
8.Operating temperature range: -25°C ~ +85°C







DETAIL A










SECTION A-A




SECTION B-B

GT-F1009 D V 44 -XX X XX 01


- **G-Switch**
- **Series No**
- **Termipoint**: D-DIP
- **Angle**: V-180°
- **Terminal Plating**: BT-Bright Tin
- **Housing Colour**: S-Nature, B-Black
- **Pin Q' PY**: 04~34
- **Height**: 44-4.40mm


Ordering Information:

Circuit	Dimensions(mm) A	B	C	Circuit	Dimensions(mm) A	B	C
04	3.00	5.10	6.00	20	19.00	21.10	22.00
05	4.00	6.10	7.00	21	20.00	22.10	23.00
06	5.00	7.10	8.00	22	21.00	23.10	24.00
07	6.00	8.10	9.00	23	22.00	24.10	25.00
08	7.00	9.10	10.00	24	23.00	25.10	26.00
09	8.00	10.10	11.00	25	24.00	26.10	27.00
10	9.00	11.10	12.00	26	25.00	27.10	28.00
11	10.00	12.10	13.00	27	26.00	28.10	29.00
12	11.00	13.10	14.00	28	27.00	29.10	30.00
13	12.00	14.10	15.00	29	28.00	30.10	31.00
14	13.00	15.10	16.00	30	29.00	31.10	32.00
15	14.00	16.10	17.00	31	30.00	32.10	33.00
16	15.00	17.10	18.00	32	31.00	33.10	34.00
17	16.00	18.10	19.00	33	32.00	34.10	35.00
18	17.00	19.10	20.00	34	33.00	35.10	36.00
19	18.00	20.10	21.00	---	---	---	---




PROPER CABLE (SCALE 2:1)





PCB REFERENCE DIAGRAM
TOLERANCE:±0.05



NO.	PART NAME	MATERIAL	REMARK
2	CONTACT	PHOSPHOR BRONZE	BRIGHT Tin
1	HOUSING	LCP,94V-0	NATURE OR BLACK

Pb Process Capable | RoHS Compliant EU RoHS Standards | Compliant Halogen Free

SCALE: 1:1	UNIT: mm	Title:	FPC 1.00mm Pitch 180° DIP Double Row Double Double Sided Welding
SIZE: A4		Model Code:	GT-F1009DV44-XXXXX01

Unless otherwise General Tolerance:
X ±0.40
X.x ±0.30
X.xx ±0.20
X° ±5°
X.x° ±3°

DRAWN	CHECKED	APPROVED	DATE
Jiang	Hu	Chen	2021.06.28

品赞科技 b-Switch www.dg-switch.com

REV: A0 SHEET: 1/1