



HAOYU

邮箱：hooya89@hooya.hk
电话：0769-82310511-867










加防水圈示意图








Pin	Signal Name	Mating Sequence	Pin	Signal Name	Mating Sequence
A1	GND	First	B12	GND	First
A2	SSTXp1	Second	B11	SSRXp1	Second
A3	SSTXn1	Second	B10	SSRXn1	Second
A4	V_{BUS}	First	B9	V_{BUS}	First
A5	CC1	Second	B8	SBU2	Second
A6	Dp1	Second	B7	Dn2	Second
A7	Dn1	Second	B6	Dp2	Second
A8	SBU1	Second	B5	CC2	Second
A9	V_{BUS}	First	B4	V_{BUS}	First
A10	SSRXn2	Second	B3	SSTXn2	Second
A11	SSRXp2	Second	B2	SSTXp2	Second
A12	GND	First	B1	GND	First
SHELL		GND	SHELL		GND

SPECIFICATION

1.Rating ：20V DC/AC
Vbus电流5A最大，GND电流5A最大，其他PIN 0.25A最大.
2.Contact resistance：≤50mΩ.
3.Insulation resistance：≥100MΩ (DC100V).
4.Withstanding voltage：100VAC .
5.INSERTION FORCE:5-20N/ REMOVAL FORCE: 8-20N
6.life test：10000 cycles.
7.Operation temperature range:-25℃~85℃.
8.Sign"* "is importance dimension.



NO.	PART NAME	MATERIAL	QTY	FINISHING
7	RUN-RING	SILICA GEL	1	BLACK
6	MIDDLE CLIP	SUS	1	
5	SHELL	SUS	1	Ni-PLATED
4	BRACKET	SUS	1	Ni-PLATED
3	CONTACT	CORSON ALLOY	24	Au-PLATED
2	SHELL HOUSING	PA10T	1	BLACK
1	REAR HIGH	PA10T	1	BLACK

TOLERANCE UNLESS SPECIFIED
<1.5: ±0.1mm
>1.5~5.0: ±0.25mm
>5.0: ±0.3mm
ANGULAR ±1°

NO	DATE	REVISIONS	BY	APPD

TITLE: USB JACK
MODEL: USB-307FSD-B-SU-003
UNIT : MM
SCALE: 1:1
ROHS COMPLIANT
DWN
CHK'D
APPD
PRO.AGL:
REV :A0

DONGGUANG HAOYU ELECTRONICS CO., LTD
皓宇东莞市弘皓电子有限公司