








Features:
1.04~40 circuits available
2.Material:PA66 UL 94V-0
3.Contact:Brass
4.Finished:Tin-plated
Specification:
1.Current rating:2A AC/DC
2.Voltage rating:100V AC/DC
3.Contact resistance:20mΩ Max.
4.Insulation resistance:1000MΩMin.
5.Withstanding voltage:800VAC/minute.
6.Ambient temperature range:-25° C~85° C.





Dimensional infotmation

PART NO.	Circuits	DIM A	DIM B
W-2022S04P-B000	4	2.00	6.00
W-2022S06P-B000	6	4.00	8.00
W-2022S08P-B000	8	6.00	10.00
W-2022S10P-B000	10	8.00	12.00
W-2022S12P-B000	12	10.00	14.00
W-2022S14P-B000	14	12.00	16.00
W-2022S16P-B000	16	14.00	18.00
W-2022S18P-B000	18	16.00	20.00
W-2022S20P-B000	20	18.00	22.00
W-2022S22P-B000	22	20.00	24.00
W-2022S24P-B000	24	22.00	26.00
W-2022S40P-B000	40	38.00	42.00



PCB LAYOUT

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO.,LTD
CHECKED:	DATE:	TITLE: 2022S-XP 双排 带扣 Pitch:2.0mm
DRAWN: YKX	DATE: 2024-07-14	PART.NO. W-2022SXXP-B000
		UNIT mm SCALE free
		FILE NO. Ckmtw-2022-0003 REV. A HC01