

Product data sheet

Characteristics

9001KS11K1H5

Harmony 9001K, selector switch, metal, key switch, 30mm, key E10, 2 positions, stay put, 1 NO



Main

Range of Product	Harmony 9001K
Product or Component Type	Selector switch
Device short name	K
Type of operator	maintained
Operator profile	Black key operated knob

Complementary

Bezel material	Metal
Mounting diameter	1.18 in (30 mm)
Operator position information	2 positions
Key number	E10
Key withdrawal position	Left
Contacts type and composition	1 NO
Connections - terminals	Screw-clamp terminals, 1 x 0.22...2 x 1.5 mm ² IEC 60947-1
Device presentation	Complete product

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901909446
Nbr. of units in pkg.	1
Package weight(Lbs)	7.68 oz (217.7 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.01 in (5.1 cm)
Package 1 width	2.52 in (6.4 cm)
Package 1 Length	4.49 in (11.4 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------