

# Product data sheet

## Characteristics

# 9001R8

Harmony 9001K, Harmony 9001SK, handle, standard handle, red, 30 mm, for selector switch



### Main

|                                       |                                 |
|---------------------------------------|---------------------------------|
| Range of Product                      | Harmony 9001K<br>Harmony 9001SK |
| Product or Component Type             | Handle                          |
| Accessory / Separate Part Type        | Knob                            |
| Accessory / separate part category    | Spare parts                     |
| Accessory / separate part destination | Selector switch                 |

### Complementary

|                             |                        |
|-----------------------------|------------------------|
| Shape                       | Standard               |
| Mounting diameter           | 1.18 in (30 mm)        |
| Cap/operator or lens colour | Red                    |
| Net Weight                  | 0.01 lb(US) (0.005 kg) |
| Operator profile            | Standard handle        |

### Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 21433-9001 ACCESS FOR K,KX,SK |
| Discount Schedule     | CS1                           |
| GTIN                  | 3389118038691                 |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 0.16 oz (4.536 g)             |
| Returnability         | Yes                           |
| Country of origin     | MX                            |

### Packing Units

|                        |                    |
|------------------------|--------------------|
| Unit Type of Package 1 | PCE                |
| Package 1 Height       | 0.70 in (1.778 cm) |
| Package 1 width        | 1.00 in (2.54 cm)  |
| Package 1 Length       | 1.00 in (2.54 cm)  |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |

|                          |  |
|--------------------------|--|
| China RoHS Regulation    | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>  |
| WEEE                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|