


4-229910-1 ACTIVE**CHAMP Docking Connectors**

TE Internal #: 4-229910-1

TE Internal Description: CLAMP, CABLE

[View on TE.com >](#)**Product Compliance**[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | CHAMP Docking Connectors




D-Sub Covers(28)



D-Sub Locking & Mounting(29)



Docking Connector Guide Hardware(5)



Docking Connectors(31)





IDC D-Sub Connectors(77)



PCB D-Sub Connectors(1)

Customers Also Bought

TE Part #5229912-1
KIT, PLUG, 50 POS,B SLOT C/LOKTE Part #3-640440-5
MTA Receptacle: Nylon, Tin Plated,
2.54 mmTE Part #1761681-3
IDC LOW PRO HDR 10P VERT HT
BLACKTE Part #5229996-3
SCREW, PAN HD, CAPTIVETE Part #1-640445-5
15P MTA156 HDR ASSY FL/STR SNLTE Part #104257-3
04 MTE RCPT HSG SR LATCH .100TE Part #104480-4
SHORT POINT CONT 30 DPLX STMPDTE Part #1658622-1
10 NOVO MIL/CTR 30DP,LEAD FREETE Part #104480-9
SHORT POINT RECP CONT LP

Documents

Product Drawings

CLAMP, CABLE

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_4-229910-1_AK.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-229910-1_AK.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-229910-1_AK.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English