

Coaxial Cable Connector 21_BNO-0-4-1/133_N

Description

Straight cable jack

Interface standards
IEC 60169-22



Technical Data

Electrical Data

Impedance	not defined Ω
Interface frequency max.	0.2 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0161 kg

Environmental Data

Operating temperature	-50 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	ETFE (Ethylene tetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00008215
Catalogue drawing	DOU-00008217
Assembly instruction	DOC-0000179394

Ordering Information

Single package	21_BNO-0-4-1/133_NE
----------------	---------------------

Additional Information

Suitable cables	RG_108_A/U
-----------------	------------