

RUGGED TIGER EYE™ SYSTEMS

(2.00 mm) .0787" PITCH



- Rugged Tiger Eye[™] contact system for high-reliability
- Wide range of stack heights (SMM/TMM Series)
- Right-angle mating headers available
- Optional metal latching, screw downs, weld tabs and locking clips
- Surface mount or through-hole
- Discrete wire assemblies available in 24-30 AWG PVC or Teflon® wire; contact asp@samtec.com for custom solutions



Optional strain relief and variety of wiring options



Components (ISD2/CC81) & tooling available: samtec.com/tooling


KEY SPECIFICATIONS (S2M/T2M)

PITCH	STACK HEIGHTS	TOTAL PINS	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	MAX CYCLES
2.00 mm	6 & 7 mm	10 - 60	Black LCP	BeCu (S2M) Phosphor Bronze (T2M)	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	3.8 A (T2M) 2.6 A (S2M (2 pins powered)	100 with 10 μ" (0.25 μm) Au





(2.00 mm) .0787" PITCH • HIGH-RELIABILITY CABLE INTERCONNECTS





T₂M Header 05, 07, 10, 15, 20, 25, 30 (Per Row)

= 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail

-TH Throughhole

-RA = Right-angle

> -SM = Surface Mount

-WT = Weld Tab (S2SD & S2SDT, -SR/-DR required mate)

-DS = Screw Down

(N/A with -RA) (mates with -S2M-DS, S2SD/S2SDT -SS/-DS option)

-K = (7.50 mm) .295" DIA Polyimide film Pick & Place Pad (-SM only)

Leave blank for tube packaging

-TR = Tape & Reel (–SM only)


-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-SM only)

Board Mates: Cable Mates: S2SD, S2SDT


T₂M



MATED HEIGHT



Note: Some lengths, styles and options are non-standard, non-returnable.



View complete specifications at: samtec.com?T2M