

Coaxial Cable Connector 21_QLA-01-2-5/112_N

Description

Straight cable jack

Interface standards

NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	1.4 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0031 kg

Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Nickel Plating

Related Documents

Outline drawing	DOU-00007991
Catalogue drawing	DOU-00007993
Assembly instruction	DOC-0000183608

Ordering Information

Bulk 100 pcs package	21_QLA-01-2-5/112_NH
----------------------	----------------------

Additional Information

Suitable cables	RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG_174_/U
-----------------	--