


Coaxial PCB Connector 85_QLA-01-0-2/112_N

Description

Right angle PCB jack

Interface Standards

NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	1.4 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0048 kg

Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00012841
Catalogue drawing	DCA-00012843
Mounting hole	DOU-00012844

Ordering Information

Single package	85_QLA-01-0-2/112_NE
----------------	----------------------

Remarks

PCB connector without stand-offs