



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 5-6609946-3  
PSJS0DSX0=C3967



TE Part # 7-6609946-9  
PSJS0SS30=C3993




TE Part # 1-6609946-9  
PSJSXSH3A=C3933




TE Part # 3-6609946-0  
PSJSXSSX0=C3944


Customers Also Bought




TE Part #3-640440-6  
MTA Receptacle: Nylon, Tin Plated,  
2.54 mm




TE Part #206306-2  
23-37 F H RECEPT REV SEX




TE Part #206306-1  
23-37 RECEPT REV SEX




TE Part #66261-4  
MALE CONTACT ASSY. (L.P.)




TE Part #66740-2  
TYPE XII FEMALE CONT (L.P.)




TE Part #640309-3  
UMNL PIN 12-10 PTPPHBZ



TE Part #282857-3  
TERMI-BLOK PCB MOUNT 90 3P.5



TE Part #1-2176388-5  
RQ 1206 14R 0.1% 10PPM 5K RL



TE Part #2-1393237-2  
RT314012F

Documents

Product Drawings  
PSJS0SSXA=C3987

English

CAD Files  
Customer View Model  
ENG\_CVM\_7-6609946-3\_A.3d\_igs.zip

English

Customer View Model



[ENG\\_CVM\\_7-6609946-3\\_A.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_7-6609946-3\\_A.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1654250-1\\_CORCOM\\_EMI\\_RFI\\_QRG](#)

English