

Within Series Adaptor 32_MFBX-50-0-1/111_N

Description

Adaptor plug/plug

MFBX plug (male) / MFBX plug (male)

Slide - snap interface

Interface standard

Series MFBX - HUBER+SUHNER MFBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Number of matings	50
Weight	0.00076 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MFBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE / LCP	

Interface - MFBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE / LCP	

Related Documents

Outline drawing	DOU-00234712
-----------------	--------------

Ordering Information

Single package	32_MFBX-50-0-1/111_NE
Bulk 100 pcs package	32_MFBX-50-0-1/111_NH-2