

Coaxial Cable Connector 11_N-50-4-11/133_N

Description

Straight cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	33 dB	28.2 dB	27.4 dB

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.024256 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00131332
Catalogue drawing	DCA-00245507
Assembly instruction	DOC-0000291824

Ordering Information

Bulk 100 pcs package	11_N-50-4-11/133_NH
----------------------	---------------------

Additional Information

Suitable cables	SX_04172_B-60, SPUMA_240, LMR-240
-----------------	-----------------------------------