

Coaxial Cable Connector 21_TNC-50-3-4/133_N

Description

Straight cable jack

Interface standards

IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0153 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Washer	PFA / PTFE	

Related Documents

Outline drawing	DOU-00007716
Catalogue drawing	DOU-00007718
Assembly instruction	DOC-0000265223

Ordering Information

Single package	21_TNC-50-3-4/133_NE
Bulk 100 pcs package	21_TNC-50-3-4/133_NH

Additional Information

Suitable cables	RG_58_C/U, RG_223_/U, ENVIROFLEX_142, RG_400_/U, ASNE0293 XF
-----------------	--