

Coaxial PCB Connector 85_MCX-75-0-1/111_N

Description

Right angle PCB jack

Interface Standards

SUHNER-MCX75

Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0016 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00012847
Catalogue drawing	DCA-00012849

Ordering Information

Single package	85_MCX-75-0-1/111_NE
Bulk 100 pcs package	85_MCX-75-0-1/111_NH

Remarks

PCB connector with stand-offs