

Coaxial Panel Connector 22_H4-50-0-15/100_N

Description

Straight bulkhead receptacle jack

Interface standards



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	0.3 GHz

Mechanical Data

Number of matings	500
Weight	0.0174 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Gasket	FKM (Fluoro elastomer, FPM)	
Fastening nut	Brass	Silver Plating
Washer	Bronze	Silver Plating

Related Documents

Outline drawing	DOU-00092457
Mounting hole	DOU-00008751

Ordering Information

Single package	22_H4-50-0-15/100_NE
----------------	----------------------

Remarks

Hermetically sealed: leak rate $\leq 10^{-6}$ Torr l/s (atm cc/s)