

Coaxial Cable Connector 16_TNC-50-7-17/133_N

Description

Right angle cable plug

Interface standards

IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	38 dB	26.8 dB	26 dB

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0364 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00141963
Assembly instruction	DOC-0000216795

Ordering Information

Single package	16_TNC-50-7-17/133_NE
----------------	-----------------------

Additional Information

Suitable cables	SPUMA_400, SPUMA_400-FR-01, Spuma_400-RS-FR, LMR-400
-----------------	--