

## Coaxial Panel Connector 22\_MBX-50-0-1/113\_N

### Description

Straight bulkhead receptacle jack

Interface standards

HUBER+SUHNER MBX



### Technical Data

#### Electrical Data

|                          |             |
|--------------------------|-------------|
| Impedance                | 50 $\Omega$ |
| Interface frequency max. | 6 GHz       |

#### Mechanical Data

|                   |     |
|-------------------|-----|
| Number of matings | 100 |
|-------------------|-----|

#### Environmental Data

|                                                      |                  |
|------------------------------------------------------|------------------|
| Operating temperature                                | -55 °C to 155 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant        |

#### Material Data

| Piece Parts    | Material         | Surface Plating       |
|----------------|------------------|-----------------------|
| Centre contact | Brass            | SUCOPRO Plating       |
| Outer contact  | Brass            | SUCOPRO Plating       |
| Body           | Brass            | SUCOPLATE (R) Plating |
| Insulator      | PFA / PTFE / LCP |                       |

### Related Documents

|                   |              |
|-------------------|--------------|
| Outline drawing   | DOU-00143045 |
| Catalogue drawing | DCA-00161882 |

### Ordering Information

|              |                      |
|--------------|----------------------|
| Tray package | 22_MBX-50-0-1/113_NY |
|--------------|----------------------|