

Coaxial PCB Connector 92_SMA-50-0-10/111_N

Description

Straight PCB jack

Interface Standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Board mounting type	edge mount
Weight	0.0044 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing	DOU-00088078
Catalogue drawing	DCA-00181402

Ordering Information

Single package	92_SMA-50-0-10/111_NE
----------------	-----------------------