

Coaxial Cable Connector 11_H4-50-3-1/133_N

Description

Straight cable plug

Interface standards



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	0.3 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0228 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00071792
Catalogue drawing	DOU-00005810
Assembly instruction	DOC-0000179536

Ordering Information

Single package	11_H4-50-3-1/133_NE
----------------	---------------------

Additional Information

Suitable cables	RG_58_C/U, G_03232, GX_03272
-----------------	------------------------------