



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (3.5% in Component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #GA1K2A1
DISCRETE 1K OHMS, +/-0.2C FROM 0C TO 25C

TE Part #1-111506-8
016 UNIV I/O 30DP SLOT LTCH

TE Part #5-146281-8
08 MODII HDR SRST B/A .100CL

TE Part #2359527-2
NECTOR T, CRIMP SOCKET CONTACT- 4.0mm2

TE Part #11026588-00
44007RC, THERM, ROHS

TE Part #T4011019041-000
M8, SCREW, MALE, S, SHIELD, 4P, GOLD

TE Part #5069806029
CGPT-1.6/0.8-0-15MM

TE Part #1337812-1
50 OHM COAX SMA ELB PLUG ELB P

TE Part #61-0152-011-000
CONTACT PIN 1,5 MM

TE Part #AEA113S06000201000
623 RECEPTACLE, SPEEDTEC-READY

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60-0173-011-000_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_60-0173-011-000_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60-0173-011-000_A1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

60-0173-011-000

English