

Coaxial Cable Connector 24_N-50-3-14/133_N

Description

Straight bulkhead cable feed through

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
Frequency range	DC to 6 GHz
Return loss	30 dB

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0399 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00008896
Catalogue drawing	DCA-00008898
Assembly instruction	DOC-0000350737

Ordering Information

Bulk 100 pcs package	24_N-50-3-14/133_NH
Single package	24_N-50-3-14/133_NE

Additional Information

Suitable cables	EZ_141_TP_M17
-----------------	---------------