

Coaxial Cable Connector 21_SK-50-2-58/199_N

Description

Straight cable jack

Interface standards
MIL-STD-348A/323



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	40 GHz
Frequency range	DC to 40 GHz
Return loss	21 dB

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0039 kg

Environmental Data

Operating temperature	-55 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	

Related Documents

Outline drawing	DOU-00078180
Catalogue drawing	DCA-00087901
Assembly instruction	DOC-0000234990

Ordering Information

Single package	21_SK-50-2-58/199_NE
----------------	----------------------

Additional Information

Suitable cables	EZ_86_M17, SUCOFORM_86, SR_86_LA
-----------------	----------------------------------