

Between Series Adaptor 33_NEX10-PC35-50-X1/1-9_N

Description

Adaptor plug/jack
NEX10 plug (male) / PC 3.5 jack (female)

For Test & Measurement applications

Interface standards
Series NEX10 - Standard
Series PC 3.5 - IEC 60169-23



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	20 GHz

Mechanical Data

Number of matings	500
-------------------	-----

Environmental Data

Operating temperature	-55 °C to 100 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - NEX10 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	Silver Plating
Body	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	

Interface - PC 3.5 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator		

Related Documents

Catalogue drawing	DCA-00343960
-------------------	--------------

Ordering Information

Single package	33_NEX10-PC35-50-X1/1-9_NE
----------------	----------------------------