

Coaxial Cable Connector 11_SMA-50-3-66/-19_N

Description

Straight cable plug

Interface standards
SUHNER-SMA-26.5GHz



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	26.5 GHz

Mechanical Data

Outer contact	soldered
Weight	0.0023 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact		
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00006516
Catalogue drawing	DOU-00006518
Assembly instruction	DOC-0000179294

Ordering Information

Bulk 100 pcs package	11_SMA-50-3-66/-19_NH
Single package	11_SMA-50-3-66/-19_NE

Additional Information

Suitable cables	EZ_141_TP_M17
-----------------	---------------