

## Within Series Adaptor 31\_N-75-0-2/133\_N

### Description

Adaptor jack/jack  
N jack (female) / N jack (female)

Interface standard  
Series N - Not compatible to N 50 Ohms



### Technical Data

#### Electrical Data

Impedance 75 Ω  
Interface frequency max. 1.5 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0386 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing DCA-00013814

### Ordering Information

Single package 31\_N-75-0-2/133\_NE