

1473562-5  ACTIVE

RITS | RITS Plug Connector

TE Internal #: 1473562-5

Standard Rectangular Connectors, Connector Assembly, Plug,
Mating Alignment, Polarization Mating Alignment Type, Mating
Retention, RITS Plug Connector

[View on TE.com >](#)



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Plug**

Mating Alignment: **With**

Mating Alignment Type: **Polarization**

Mating Retention: **With**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Contacts Preloaded	Yes
Number of Positions	5
Number of Rows	1

Electrical Characteristics

Operating Voltage	32 VDC
-------------------	--------

Contact Features

Contact Layout	Inline
Contact Type	Tab

Wire Contact Termination Area Plating Material

Gold

Contact Underplating Material

Nickel

Contact Mating Area Plating Material

Gold

Contact Retention Within Housing

Without

Contact Current Rating (Max)

3 A

Termination Features

Termination Method to Wire & Cable

Crimp

Mechanical Attachment

PCB Mount Alignment

Without

PCB Mount Retention

Without

Mating Alignment

With

Mating Alignment Type

Polarization

Mating Retention

With

Mating Retention Type

Latch

Connector Mounting Type

Cable Mount (Free-Hanging)

Housing Features

Housing Material

Thermoplastic GF

Housing Color

Yellow

.079 in

Dimensions

Connector Height

18.5 mm[.728 in]

Product Width

5.05 mm[.198 in]

Product Length

20.1 mm[.791 in]

Usage Conditions

Operating Temperature Range

-30 – 75 °C[-22 – 167 °F]

Operation/Application

Halogen Free

Yes

Shielded

No

Circuit Application

Signal

Identification Marking

Circuit Identification Feature

Without

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	25
Packaging Method	Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1729940-1
RITS HAND TOOL

Also in the Series | RITS Plug Connector



Standard Rectangular Connectors(32)

Customers Also Bought

TE Part #5749621-4
40 50S CABLE PLUG CONN/COV KITTE Part #3-178140-2
DYNAMIC D3200 HDR V ASSY 6PTE Part #2-1623732-8
Wirewound Resistor: Vertical MountTE Part #1747443-6
DYNAMIC D-5 TAB CONTACT_L-SIZETE Part #1473562-6
RITS CONN. PLUG ASSY 6P YELLOWTE Part #1473565-6
RITS CONN.HDR ASSY 6PTE Part #1-172159-9
MINI UNIVERSAL M-N-L CAP 4PTE Part #2-2176331-5
CRGP 2512 1K0 1%

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_1473562-5_F.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model[ENG_CVM_CVM_1473562-5_F.3d_igs.zip](#)

English

Customer View Model[ENG_CVM_CVM_1473562-5_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[Remote Input Output Terminal System \(RITS\) Connectors](#)

English

Product Specifications[Product Specification](#)

Japanese

Instruction Sheets[Instruction Sheet \(non U.S.\)](#)

Japanese

[RITS Connector Interconnection System/e-CON Connector](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[HAND TOOL FOR RITS PLUG SOCKET ASSEMBLY](#)

Japanese