

Between Series Adaptor 33_BNC-SMB-50-2/1--_U

Description

Adaptor plug/jack
BNC plug (male) / SMB jack (female)

Interface standards

Series BNC - IEC 61169-8_MIL-STD-348A/301_CECC 22120

Series SMB - IEC 60169-10_MIL-STD-348A/311_CECC 22130



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz
VSWR	DC - 4 GHz ≤ 1.06 + 0.04 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.0113 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - BNC plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - SMB jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00014377
-------------------	--------------

Ordering Information

Single package	33_BNC-SMB-50-2/1--_UE
----------------	------------------------