

Coaxial Cable Connector 16_BNC-50-3-26/133_N

Description

Right angle cable plug

Interface standards

IEC 61169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	4 GHz	
Frequency range	DC to 2.5 GHz	2.5 to 4 GHz
Return loss	32 dB	19 dB

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0161 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00109810
Assembly instruction	DOC-0000179021

Ordering Information

Single package	16_BNC-50-3-26/133_NE
----------------	-----------------------

Additional Information

Suitable cables	RG_223_/U, ENVIROFLEX_142, G_03232_D-01, RG_400_/U, RADOX_RF_400
-----------------	--

Remarks

El. optimized for cable RG_223_/U