

Between Series Adaptor 33_N_4310-50-1/133_N

Description

Adaptor plug/jack
N-precision plug (male) / 4.3-10 jack (female)

Interface standards
Series N-precision - IEC 61169-16_MIL-STD-348A/304_CECC 22210
Series 4.3-10 - IEC 61169-54



Technical Data

Electrical Data

Interface frequency max.	12 GHz	
Frequency range	DC to 4 GHz	4 to 6 GHz
Return loss	≥ 36 dB	≥ 32 dB

Mechanical Data

Number of matings	500
Weight	0.047196 kg

Environmental Data

Operating temperature	-55 °C to 90 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - N-precision plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

Interface - 4.3-10 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00253226
-----------------	--------------

Ordering Information

Single package	33_N_4310-50-1/133_NE
----------------	-----------------------