

Coaxial Panel Connector 23_C-50-0-1/133_N

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-7_MIL-STD-348A/302



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Number of matings	500
Weight	0.0226 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00162688
Catalogue drawing	DCA-00010390

Ordering Information

Single package	23_C-50-0-1/133_NE
----------------	--------------------