

Coaxial Cable Connector 25_BMA-N50-2-13/119_N

Description

Straight panel cable jack, flange mount

Interface standards

IEC 60169-33_MIL-STD-348/321 fully intermateable



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	plugged
Outer contact	soldered

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Other body part	Stainless Steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing	DOU-00129008
Assembly instruction	DOC-0000230377
Mounting hole	DOU-00008816

Ordering Information

Single package	25_BMA-N50-2-13/119_NE
----------------	------------------------

Additional Information

Suitable cables	EZ_86_TP_M17, SUCOFORM_86
-----------------	---------------------------