

Within Series Adaptor 43_QLA-01-0-1/112_N

Description

T-adaptor, 2 jacks, 1 plug
QLA-01 jack (female) / QLA-01 plug (male)



Interface standard
Series QLA-01 - NIM-CAMAC-Standard CD/N549

Technical Data

Electrical Data

Impedance other Ω
Interface frequency max. 1.4 GHz

Mechanical Data

Number of matings 10000
Weight 0.0071 kg

Environmental Data

Operating temperature -55 °C to 150 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact		Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Interface - QLA-01 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact		Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	Nickel Plating

Related Documents

Catalogue drawing DPA-00036612

Ordering Information

Single package 43_QLA-01-0-1/112_NE