

Coaxial Panel Connector 23_BNO-0-0-2/133_N

Description

Straight panel receptacle jack, flange mount

Interface standards
IEC 60169-22



Technical Data

Electrical Data

Impedance	not defined Ω
Interface frequency max.	0.2 GHz

Mechanical Data

Number of matings	500
Weight	0.0102 kg

Environmental Data

Operating temperature	-50 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	ETFE (Ethylene tetrafluoroethylene)	

Related Documents

Outline drawing	DOU-00010819
Catalogue drawing	DCA-00010821
Mounting hole	DOU-00009051

Ordering Information

Single package	23_BNO-0-0-2/133_NE
----------------	---------------------