


Coaxial PCB Connector 85_QMA-50-0-3/111_N

Description

Right angle PCB jack

Interface Standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0041 kg

Environmental Data

Operating temperature -40 °C to 85 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00012659
Catalogue drawing DCA-00012661
Mounting hole DOU-00002524

Ordering Information

Bulk 100 pcs package 85_QMA-50-0-3/111_NH

Remarks

PCB connector with stand-offs