

Coaxial Cable Connector 14_BMA-50-3-32/133_N

Description

Straight bulkhead cable plug

Interface standards

BMA Economic (mech. compatible with BMA Std acc. to Mil)



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12.4 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00230460
Catalogue drawing	DCA-00238082
Assembly instruction	DOC-0000408386
Mounting hole	DOU-00008972

Ordering Information

Bulk 100 pcs package	14_BMA-50-3-32/133_NH
----------------------	-----------------------

Additional Information

Suitable cables	RG_223_/U, RG_400_/U, RG_142_B/U, RADOX_RF_400
-----------------	--