

ATGBICS 100GQSFP-LR4-4 Cisco Compatible Transceiver QSFP28

100GBase-LR4 (1310nm, SMF, 10km, LC, DOM)

Brand : ATGBICS

Product code: 100GQSFP-LR4-4-C



Product name : 100GQSFP-LR4-4 Cisco Compatible Transceiver QSFP28 100GBase-LR4 (1310nm, SMF, 10km, LC, DOM)


100GQSFP-LR4-4 Cisco Compatible Transceiver QSFP28 100GBase-LR4 (1310nm, SMF, 10km, LC, DOM)

ATGBICS 100GQSFP-LR4-4 Cisco Compatible Transceiver QSFP28 100GBase-LR4 (1310nm, SMF, 10km, LC, DOM):

ATGBICS 100GQSFP-LR4-4 100GBase-LR4 QSFP28 supports a distance of up to 10Km over single-mode fibre (SMF) using a wavelength of 1310nm via an LC connector. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product meets the specification of 100GQSFP-LR4-4= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



Performance		Features	
SFP transceiver type *	Fiber optic	Brand compatibility	Cisco
Maximum data transfer rate *	100000 Mbit/s	Certification	CE, FCC, RoHS
Interface type *	QSFP28	Power	
Single-mode fiber (SMF) supported	✓		Input voltage
Multi-mode fiber (MMF) supported	✗		Maximum voltage
Fiber optic connector	LC		Power consumption (typical)
SFP transceiver standard	LR4	Operational conditions	
Maximum transfer distance	10000 m	Operating temperature (T-T)	0 - 70 °C
Wavelength	1310 nm	Storage temperature (T-T)	-40 - 85 °C
Ethernet LAN	✓	Operating relative humidity (H-H)	0 - 95%
Ethernet interface type	100 Gigabit Ethernet	Storage relative humidity (H-H)	0 - 95%
Networking standards	IEEE 802.3ba, IEEE 802.3bm	Weight & dimensions	
Digital Diagnostics Monitoring (DDM)	✓	Width	13.5 mm
Features		Depth	72.4 mm
Product colour	Silver	Height	18.4 mm
Housing material	Metal	Weight	42 g
Plug and Play	✓	Packaging data	
Hot-Plug support	✓	Number of products included	1 pc(s)
Hot-swap	✓	Package type	Box
Easy to install	✓	Technical details	
Country of origin	United Kingdom	Sustainability compliance	✓
		Sustainability certificates	RoHS
		Doesn't contain	Lead



5056468748607

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.