



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 360050-1 090 DIA CLSTR BLK	 TE Part # 1969357-1 HSG .090 CLUSTER BLOCK 2 POS	 TE Part # 880631-5 CLUSTER BLOCK HSG .090 DIA	 TE Part # 1955415-1 3P CLUSTER BLOCK HOUSING
 TE Part # 2232327-1 CLUSTER BLOCK HSG .090 DIA	 TE Part # 284406-3 CLUSTER BLOCK HSG .090 DIA. RE	 TE Part # 235280-1 CLUSTER BLOCK HSG .090 DIA	 TE Part # 1380145-1 CLUSTER BLOCK HSG .090 DIA
 TE Part # 2232326-1 CLUSTER BLOCK HSG .090 DIA	 TE Part # 281006-4 CLUSTER BLOCK .090 DIA	 TE Part # 1217262-1 HSG .090 CLUSTER BLOCK NAT	 TE Part # 360033-1 090 DIA CLSTR BLK
 TE Part # 1217263-1 HSG .090 CLUSTER BLOCK NAT	 TE Part # 1380145-2 CLUSTER BLOCK HSG .090 DIA	 TE Part # 2-2150262-2 OCEAN_2.0_APPLICATOR-E-110F155F	 TE Part # 2150262-2 OCEAN_2.0_APPLICATOR-E-110F155F
 TE Part # 2161850-4 APT-5A DIRECT CONNECT	 TE Part # 2232326-2 CLUSTER BLOCK HSG .090 DIA	 TE Part # 2232327-2 CLUSTER BLOCK HSG .090 DIA	 TE Part # 521078-1 CLUSTER BLOCK HSG 090DIA WHT

Customers Also Bought






TE Part #8-1393113-7
KUEP-11D15-24=KU-



TE Part #3-520151-2
ULTRAFAST 187 ASSY REC 16-14
TPBR LP



TE Part #1393143-6
27E122=SOCKET,KRP,8,SCW,PLES




TE Part #35107
TERMINAL,PIDG R 12-10 6



TE Part #1-1423157-2
7012AE=RLY,STD,ON,2P,120VAC,20



TE Part #34149
PG R 22-16 COMM 22-18 MIL 10



TE Part #3-520141-2
ULTRAFAST 250 ASSY REC 16-14
TPBR LP



TE Part #1423157-2
7012AB=RLY,STD,ON,2P,120VAC,5S

TE Part #4-1393159-8
20C318=SPRING,HOLD-DOWN,K10,0



TE Part #3-1437466-5
VMAXBA=*

Documents

Product Drawings

2.29 DIA CLUSTER PIN AMPLV REC 1600-4800

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1742964-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1742964-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1742964-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English