

Coaxial Cable Connector 24_SK-50-2-55/1--_N

Description

Straight bulkhead cable feed through

Interface standards
MIL-STD-348A/323



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	40 GHz		
Frequency range	DC to 12 GHz	12 to 28 GHz	28 to 40 GHz
Return loss	25 dB	20 dB	15 dB

Mechanical Data

Centre contact	plugged
Outer contact	soldered

Environmental Data

Operating temperature	-55 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Stainless Steel	Passivated (Plating)
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00070579
Catalogue drawing	DCA-00089477
Assembly instruction	DOC-0000229976
Mounting hole	DOU-00008731

Ordering Information

Single package	24_SK-50-2-55/1--_NE
----------------	----------------------

Additional Information

Suitable cables	EZ_118_TP
-----------------	-----------