

Coaxial Cable Connector 11_N-50-3-51/133_N

Description

Straight cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0435 kg

Environmental Data

Operating temperature	-55 °C to 70 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	Air Dielectric - Bead - PPH	
Coupling nut	Brass	SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DOU-00007863
Assembly instruction	DOC-0000180866

Ordering Information

Single package	11_N-50-3-51/133_NE
----------------	---------------------

Additional Information

Suitable cables	SUCOFORM_141, EZ_141_TP_M17, MULTIFLEX_141
-----------------	--