

Data sheet

2848.0 H 4,0/18-D GR



Wire-end ferrules, Max. wire cross-section: 4 mm², Length: 18 mm, Length of copper pipe: 10 mm, Colour: Grey

RAL: Ähnlich 7035

Business data

Article number	2848.0
Article name	H 4,0/18-D GR
GTIN (EAN)	4044211055738
Packaging unit	500
Quantity unit	PC
Weight per piece (not including packaging)	0.25 g
Weight per piece (including packaging)	0.26 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Grey

Data sheet

2848.0 H 4,0/18-D GR

Technical data

Dimensions

Length	18 mm
Length of copper pipe	10 mm
Diameter of copper pipe	2.8 mm
Diameter plastic collar	4.8 mm
Wall thickness of copper pipe	0.2 mm
Wall thickness of plastic collar	0.3 mm

Connection data

Wire cross-section, max.	4 mm ²
Wire cross-section AWG, max.	12
Stripping length	12 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2848.0 H 4,0/18-D GR



Approvals

Standards and regulations

DIN 46228-4:1990	yes
------------------	-----

Media

Accessories
