

Coaxial Cable Connector 16_MMBX-50-2-2/111_N

Description

Right angle cable plug

Interface standards
SUHNER-MMBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12.4 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0011 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00006252
Catalogue drawing	DOU-00006254
Assembly instruction	DOC-0000178673

Ordering Information

Single package	16_MMBX-50-2-2/111_NE
Bulk 100 pcs package	16_MMBX-50-2-2/111_NH

Additional Information

Suitable cables	ENVIROFLEX_316_D, K_02252_D, G_02232_D
-----------------	--