

Coaxial Cable Connector 21_MMCX-50-1-2/111_O

Description

Straight cable jack

Interface standards
SUHNER-MMCX

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0008 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	Gold Plating (without Nickel underplating)

Related Documents

Catalogue drawing	DOU-00005909
Assembly instruction	DOC-0000179110

Ordering Information

Single package	21_MMCX-50-1-2/111_OE
----------------	-----------------------

Additional Information

Suitable cables	K_01152-07
-----------------	------------