

Coaxial Cable Connector 24_SMA-50-2-46/133_N

Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0044 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00008866
Catalogue drawing	DCA-00008868
Assembly instruction	DOC-0000179078
Mounting hole	DOU-00008748

Ordering Information

Bulk 100 pcs package	24_SMA-50-2-46/133_NH
Single package	24_SMA-50-2-46/133_NE

Additional Information

Suitable cables	RG_316_/U, RG_188_A/U, RG_174_/U
-----------------	----------------------------------