

Between Series Adaptor 34_MCX-N-50-1/133_U

Description

Bulkhead adaptor jack/jack
MCX jack (female) / N jack (female)

Interface standards
Series MCX - IEC 60169-36_CECC 22220
Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz
VSWR	DC - 6 GHz ≤ 1.08 + 0.02 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.0238 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MCX jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00014130
Mounting hole	DOU-00008751

Ordering Information

Single package	34_MCX-N-50-1/133_UE
----------------	----------------------