

Coaxial Cable Connector 11_SMB-50-2-40/111_NH-1

Description

Straight cable plug

Interface standards

IEC 60169-10_MIL-STD-348A/311_CECC 22130



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0021 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PSU (Polysulfone)	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Catalogue drawing	DOU-00006508
Assembly instruction	DOC-0000179013

Ordering Information

Bulk 100 pcs package	11_SMB-50-2-40/111_NH-1
----------------------	-------------------------

Additional Information

Suitable cables	RG_316_/U, RG_174_/U
-----------------	----------------------