

ATGBICS CVR-QSFP-SFP10G Cisco Compatible Transceiver Adapter Converter Module 40G QSFP+ to 10G SFP+

Brand : ATGBICS

Product code: CVR-QSFP-SFP10G-C

Product name : CVR-QSFP-SFP10G Cisco Compatible Transceiver Adapter Converter Module 40G QSFP+ to 10G SFP+

CVR-QSFP-SFP10G Cisco Compatible Transceiver Adapter Converter Module 40G QSFP+ to 10G SFP+

ATGBICS CVR-QSFP-SFP10G Cisco Compatible Transceiver Adapter Converter Module 40G QSFP+ to 10G SFP+:

ATGBICS compatible CVR-QSFP-SFP10G Adapter Converter Module provides the ability to convert QSFP+ to SFP+. This product enables simple, cost effective connections between quad lane ports such as 40 Gigabit Ethernet adapters using QSFP+ and 10 Gigabit Ethernet hardware using SFP+ based cabling. Our rigorously tested products are compliant to MSA standards and protocols including; SFF-8431 SFP+ and SFF-8436 QSFP+ and we proudly offer a compatibility guarantee and lifetime warranty. ATGBICS CVR-QSFP-SFP10G Cisco Compatible Transceiver Adapter Converter Module 40G QSFP+ to 10G SFP+. SFP transceiver type: Fiber optic, Maximum data transfer rate: 40000 Mbit/s, Interface type: QSFP+. Product colour: Silver, Country of origin: United Kingdom, Brand compatibility: Cisco. Package type: Box



Performance		Operational conditions	
SFP transceiver type *	Fiber optic	Minimum operating temperature	-20 °C
Maximum data transfer rate *	40000 Mbit/s	Maximum operating temperature	85 °C
Interface type *	QSFP+	Operating temperature (T-T)	-20 - 85 °C
Fiber optic connector	MPO	Packaging data	
Ethernet LAN	✓	Package type	Box
Ethernet interface type	10 Gigabit Ethernet	Technical details	
Features		Sustainability compliance	✓
Product colour	Silver	Sustainability certificates	RoHS
Country of origin	United Kingdom	Doesn't contain	Lead
Brand compatibility	Cisco		
Certification	CE, FCC, RoHS		



5056468729231

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 14-SEP-2023. Prints or copies of Information are only valid on the printed Publication date