

ATGBICS SFP-OC12-LR2 Cisco Compatible Transceiver SFP OC-12/STM-4 (1310nm, SMF, 80km, DOM)

Brand : ATGBICS

Product code: SFP-OC12-LR2-C

Product name : SFP-OC12-LR2 Cisco Compatible
Transceiver SFP OC-12/STM-4 (1310nm, SMF, 80km, DOM)



SFP-OC12-LR2 Cisco Compatible Transceiver SFP OC-12/STM-4 (1310nm, SMF, 80km, DOM)

ATGBICS SFP-OC12-LR2 Cisco Compatible Transceiver SFP OC-12/STM-4 (1310nm, SMF, 80km, DOM):

ATGBICS SFP-OC12-LR2 OC-12 (622mbs) supports a distance of up to 80km over single mode fibre (SMF) using a wavelength of 1310nm via an LC connector. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product meets the specification of Cisco SFP-OC12-LR2= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



Performance

SFP transceiver type *	Fiber optic
Maximum data transfer rate *	622 Mbit/s
Interface type *	SFP
Single-mode fiber (SMF) supported	✓
Multi-mode fiber (MMF) supported	✗
Fiber optic connector	LC
Maximum transfer distance	80000 m
Wavelength	1310 nm
Ethernet LAN	✓
Ethernet interface type	Fast Ethernet
Digital Diagnostics Monitoring (DDM)	✓

Features

Product colour	Silver
Housing material	Metal
Plug and Play	✓
Hot-swap	✓
Easy to install	✓
Country of origin	United Kingdom
Brand compatibility	Cisco
Certification	CE, FCC, RoHS

Power

Input voltage	3.3 V
Maximum voltage	3.5 V
Power consumption (typical)	1 W

Operational conditions

Maximum operating temperature	70 °C
Operating temperature (T-T)	0 - 70 °C
Storage temperature (T-T)	-40 - 85 °C
Operating relative humidity (H-H)	0 - 95%
Storage relative humidity (H-H)	0 - 95%

Weight & dimensions

Width	12.7 mm
Depth	55.9 mm
Height	7.62 mm
Weight	19 g

Packaging data

Number of products included	1 pc(s)
Package type	Box

Technical details

Sustainability compliance	✓
Sustainability certificates	RoHS
Doesn't contain	Lead



5056468707437

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 14-SEP-2023. Prints or copies of Information are only valid on the printed Publication date