

ATGBICS 7118021 Sun Oracle Compatible Transceiver SFP28 25GBase-LR (1310nm, SMF, 10km, DOM)

Brand : ATGBICS**Product code:** 7118021-C**Product name :** 7118021 Sun Oracle Compatible
Transceiver SFP28 25GBase-LR (1310nm, SMF, 10km, DOM)

Sun Oracle Compatible Transceiver SFP28 25GBase-LR 1310nm SMF 10km DOM

ATGBICS 7118021 Sun Oracle Compatible Transceiver SFP28 25GBase-LR (1310nm, SMF, 10km, DOM):

ATGBICS 7118021 25GBase-LR supports a distance of up to 10km over single-mode fibre (SMF) using a wavelength of 1310nm via an LC connector. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product is built to the exact specification of Sun Oracle 7118021= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



Performance		Features	
SFP transceiver type *	Fiber optic	Country of origin	China
Maximum data transfer rate *	25000 Mbit/s	Brand compatibility	Sun
Interface type *	SFP	Power	
Single-mode fiber (SMF) supported	✓	Input voltage	3.3 V
Multi-mode fiber (MMF) supported	✗	Maximum voltage	3.5 V
Fiber optic connector	LC	Power consumption (typical)	1 W
SFP transceiver standard	LR	Operational conditions	
Maximum transfer distance	10000 m	Maximum operating temperature	70 °C
Wavelength	1310 nm	Operating temperature (T-T)	0 - 70 °C
Ethernet LAN	✓	Storage temperature (T-T)	-40 - 85 °C
Ethernet interface type	25 Gigabit Ethernet	Operating relative humidity (H-H)	0 - 95%
Digital Diagnostics Monitoring (DDM)	✓	Storage relative humidity (H-H)	0 - 95%
Wavelength-division multiplexing (WDM)	✗	Weight & dimensions	
Features		Width	13.4 mm
Product colour	Silver	Depth	56.5 mm
Housing material	Metal	Height	8.5 mm
Plug and Play	✓	Weight	19 g
Hot-Plug support	✓	Packaging data	
Hot-swap	✓	Number of products included	1 pc(s)
Easy to install	✓	Package type	Box
		Technical details	
		Sustainability certificates	RoHS



5056468760760

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 14-SEP-2023. Prints or copies of Information are only valid on the printed Publication date